PPE & Site Safety

Take a look at a selection of our wide range of products and brands to support all your PPE and Site Safety needs.

Whatever type of business you are in, we're by your side.

za.rs-online.com / www.rsonline.africa

PPE
PAGE 2

WORKWEAR
PAGE 6

SITE SAFETY
PAGE 9

Evo 2 Safety Helmets

- Tough HDPE helmet shell with 3D precision fitting using the unique 1-2-3 point harness depth settings
- One touch slip ratchet simple to fit and adjust
- Side and rear ventilation, and universal slots enabling firm fitting of safety visors and ear defenders
- 440Vac electrical insulation and molten metal resistance

JSP

750-6763	Blue
750-6766	Green
750-6779	Orange
750-6760	Red
750-6750	White
750-6754	Yellow

Optime Ear Defenders

- High-performance ear defenders with different SNR ratings to meet the requirements of the environment
- Soft wide cushions help reduce pressure around the ears and improve comfort and wearability
- Large space inside cup helps reduce moisture and heat build-up
- Easy to replace cushions and inserts to help keep them hygienically clean

3M Peltor™

449-6477	Yellow Optime I SNR 28dB
449-6483	Green Optime II SNR 31dB
449-6499	Black/Red Optime III SNR 35dB

Short Peaked Bump Caps

- Adjustable cap offers protection from minor head scrapes, bumps and lacerations
- The high-profile ABS shell acts as a shock absorber and comes with a soft padded crown, giving optimum safety and protection for the wearer
- Features a short peak of 3cm which allows for increased upward and better peripheral visibility

RS PRO

918-5680	Black
918-5699	Navy

RS PRO Corded Disposable Ear Buds

- Designed to fit the contour of the ear, the earplugs are easy to insert and remove
- Disposable means there are no cleaning or maintenance concerns
- Noise reduction rating of 32dB
- Supplied and priced as box of 200



RS PRO

918-5696

Uvex Disposable Earplugs

- Easy to grip
- Exceptional comfort and extra-low pressure in the ear canal
- Low sound absorption
- More natural sound
- No risk of over protection

uvex

168-1683	100 pairs
168-1684	100 pairs
168-1687	250 pairs

Ansell

HyFlex® 11-840

- These industrial hand gloves provide extreme durability for extended wear in abrasive applications, with up to 20% higher protection and up to 2 times more grip in dry environments
- Thin FORTIX™ nitrile foam coating is softer which increases flexibility and comfort offering 20% longer wear time
- Ansell ZONZ™ Comfort Fit Technology optimises the knitting of the liner improving support, breathability and range of movement

791-7514	Size 8
791-7523	Size 9
791-7526	Size 10

TouchNTuff® 92-600

- The world's leading disposable glove for chemical splash protection provided by the material formulation which also offers high levels of comfort
- Robust design for superior durability
- Silicone free design is paint and finish process friendly

261-6641	6.5 - small (box of 100)
261-6736	7.5 - medium (box of 100)
261-6720	8.5 - large (box of 100)

AlphaTec® Solvex® 37-675

- Versatile flocked glove with Sandpatch finish providing a smooth surface suitable for use across a diverse range of applications
- Fully reusable, with superb comfort for the wearer
- Complies with FDA food handling requirements (21 CFR 177.2600)

186-3492	Size 8 (bag of 5)
186-3509	Size 9 (bag of 5)
667-9762	Size 10 (bag of 5)

G791 Work Gloves

- Ideal choice for users undertaking more intricate work
- PU palm coating offers an enhanced grip

RELDEEN

221-4834	Size 7 (bag of 12)
221-4835	Size 8 (bag of 12)
221-4836	Size 9 (bag of 12)
221-4837	Size 10 (bag of 12)

Rigger Gloves

- High quality, cow split leather and cotton work gloves for ultimate protection and comfort in tough and hazardous environments
- Elasticated safety cuff keeps the gloves safely in position and soft cotton liner gives increased comfort and breathability when working

RS PRO

184-8055	

Cut Resistant Gloves for Food Industry

- Suitable for butchery, fish filleting and meat processing
- Highly durable performance delivering EN388: 2016 level E cut resistance
- Can be washed up to 95°C for 1 minute for thermal disinfection

PROFIT

219-8040	X-small
219-8041	Small
219-8043	Medium
219-8044	Large
219-8045	X-large

3M Science. Applied to Life.™

Welcome to your comfort zone.

3M™ Versaflo™ Powered Air Respirator Systems

LEARN MORE

3M™ Versaflo™ Powered Air Turbo TR-600

- Delivers protection, comfort and performance
- Designed for tough environments including metalworking, grinding and welding
- Provides protection against particles, gases and vapours
- Helps make breathing and working easier

Controlled airflow – delivers steady flow as battery discharges or filter loads with particles
Increased battery performance – long run times, less charging time
Comfortable airflow – three user selectable flow rates to maximise comfort
Ease of use – audible, visual and vibratory electronic alarm in case of low battery or low air flow

Starter Kit includes the TR-602E turbo unit, A2P filter, filter cover, prefilters (x10), easy clean belt, battery, battery charger kit, BT-30 breathing tube, airflow indicator and spark arrestor (x2).

197-6471	TR-619UK starter kit	**712-8613**	S-433L hood
828-5681	M-306 helmet	**712-8616**	S-133L head cover

Auto-darkening Welding Helmet

- Switches from a light to dark state when welding activity starts
- Dark state is adjustable from DIN 9 to DIN 13 using the external knob
- Fast response time from light to dark state and in reverse
- Power is supplied by solar cells with 2 built-in lithium batteries to offer back-up for longer service life

RS PRO

171-6848

A800 Clear Safety Glasses

- Frame with integrated side protection in the straight arms, fitted with soft rubber temple-tips and a non-slip soft rubber nose piece
- For general use and impact protection (45m/s)
- Polycarbonate shield with anti-scratch treatment and 99.9% UV protection

Honeywell

104-0947	Clear
104-0948	Anti-fog clear

Uvex Ultravision Anti-Mist Safety Goggles

- Classic, ergonomic wide-vision goggle with unrestricted side visibility
- Lenses can be replaced
- Colour of frame: transparent grey
- Clear CA lens
- Reliable UV 380 protection

uvex

185-3495

8822 Particulate Respirator P2 Valved

- For mechanically and thermally generated particles and fumes, e.g., grinding, sanding, crushing, sawing, smoke and welding
- 3M™ Advanced Electret filter material gives effective filtration with low breathing resistance for consistent high quality performance
- 3M™ Cool Flow™ exhalation valve offers improved comfort in hot humid environments

3M

766-160 FFP2 box of 10

X-plore Half Respirator Mask

- Economical, easy to maintain, good wearing comfort
- Mask body made from Soft-TPE or DraegerFlex material (silicon free)
- Comfortable and easy respiration with low resistance
- Innovative product features ensure optimal safety

Dräger

221-8567	3300 S
221-8569	3500 M
221-8571	3500 L

ECO-PACKAGING

100% RECYCLABLE PACKAGING

30% LESS WASTE

VEGETAL BASED INK

bollé SAFETY

"We all have a role **to play in protecting the planet.**"

Since the launch of our *GO GREEN* plan, our eco-conscious projects flourished for the greatest benefits of both our customers and the planet. We are proud to provide a 100% recyclable packaging made of recycled cardboard and silk paper. We also took the decision to print our user instructions directly on our master packaging with vegetal-based ink. No plastic, less waste.

NYLON FRAME MADE OF RECYCLED FISHING NET

bolle-safety.com

Soft Shell Jackets

- Stylish and comfortable softshell jacket providing an outer layer of protection
- Zip front fastening with an inner storm flap for extra protection
- Also available in blue - visit our website for more options

136-9986	S
136-9985	M
136-9983	L
136-9987	XL
136-9982	XXL

Hi-Vis Sweatshirt

- No need for additional hi-vis vests, wear this sweatshirt that has the reflective tape on it already
- Long sleeved polyester and cotton material that is ideal for cooler weather
- Also available in yellow - visit our website for more details

141-7756	S
141-7757	M
141-7758	L
141-7759	XL

Xelerate Metal Free Safety Trainers

- Ultra-flexible, safety knit textile fabric perfectly adapts to the foot
- Classical design elements are combined with a modern fashionable cut
- Safety Rating: S1 P SRC HRO; 200J composite toe cap

161-7420	Size 6
161-7421	Size 7
161-7422	Size 8
161-7423	Size 9
161-7424	Size 10
161-7425	Size 11
161-7426	Size 12

za.rs-online.com / www.rsonline.africa

uvex

Designed with you in mind

uvex understands that everyone is an individual and when it comes to PPE, one size does not fit all. It may seem obvious but correctly sized PPE can help avoid accidents, reduce distress and discomfort; and increase productivity.

uvex is committed to the design and production of product solutions that can be tailored to individual requirements delivering absolute consistency of protection and performance levels.

Uvex PHEOS Guard S
Safety Eyewear

- Duo-spherical lens
- Scratch resistant
- Anti-fog interior

Click to find out more

Uvex phynomic lite
Safety Gloves

- Excellent blade cut resistance, very high abrasion resistance, very high tear resistance
- Lightweight & sensitive cut protection glove for mechanical activities
- Available in sizes: 6 to 12

Click to find out more

Uvex 1
Safety Footwear

- Lightweight with breathable
- High level of cushioning
- Shock absorbing sole
- Protection class S1 SRC
- Metal-free toe cap
- Available in sizes: 35 to 50

Click to find out more

H Design 2 Point Harness

- Complete with mating buckles on the chest and leg straps plus 2 sternal webbing loops, this new generation harness provides you with comfort and freedom of movement providing security to workers
- Adjustable chest and leg straps ensure a remarkably versatile harness
- Horizontal leg straps prevent uncomfortable friction and the H architecture of the harness gives total freedom for legs and arms

MILLER by Honeywell

104-0877	T. 1 : 1032839 small/medium
104-0878	T. 2 : 1032840 medium/large
104-0879	T. 3 : 1032841 large/extra large

Spartan Height Safety Kits

- Kits include harness (1 or 2 point)
- Lanyard: 1.8m fixed length (restraint kit) or 2m fall arrest (fall arrest kit)
- Plus JSP® woven draw-string bag

JSP

861-0403	Restraint kit (1 point harness)
861-0406	Fall arrest kit (2 point harness)

Height Safe Carabiners

- Perfect for working at height to reduce injury and damage or loss of tools
- Stainless steel construction with excellent corrosion resistance
- Quick and easy to attach or detach tools and other equipment with a non-lock snap design
- Available with a choice of sizes to accommodate numerous tasks

FACOM

910-3350	300kg 60mm

SAFETY IN NUMBERS. OUR RANGE OF PPE.

The huge range of RS PRO PPE products means you'll always find what you need to stay safe.

rspro.com

22 Litre Spill Kits

- Be prepared with these Spill & Go kits designed to offer a practical yet cost effective solution for dealing with small spills and leaks
- Kits contain 20 × Premier 50 × 40cm pads, 1.2m Premier sock in a handy bag with handle
- Other sizes available - visit our website for more details

ecospill

192-7747	Chemical
192-7755	Maintenance
192-7751	Oil

Retractable Wall Mount Barriers

- Used to prevent pedestrians or traffic from gaining access to restricted areas or floor space
- Water-proof case with a retractable belt made from high-quality tear-proof materials and a connecting wall receiver
- Easy to install

RS PRO

217-5268	Black / yellow 50mm x 4m
217-5269	Red / white 50mm x 4m
217-5266	Black / yellow 50mm x 10m
217-5267	Red / white 50mm x 10m

Sharps Disposal Refill

- Bright yellow plastic with visible warnings
- Clinical self seal bags, 28´19cm
- Heavy duty biohazard bag, 45´75cm

RS PRO

195-4908

Spill Absorbent Granules

- Highly effective general purpose absorbent suitable for controlling industrial/commercial leaks and spills such as oil, paint, water
- Easy to use and non toxic
- 35 litre bag

PYRASORB

174-7946

Helix Road Cone

- Spiral 'helix' design greatly improves wind deflection compared to standard cones thus improving stability
- Specially-constructed glass-bead sleeve offers twice the light reflectivity of standard, prismatic alternatives
- 750mm high



Skipper™
The total safety management solution

885-3596

Site Transformer

- Portable isolation transformer
- 5-minute short time
- Primary voltage rating of 230 V AC

RS PRO

123-7381	375VA Isolation Transformer

Rubbermaid Commercial Products

ESSENTIAL SAFETY & WASTE SOLUTIONS

THE MOBILE BARRIER IS EASY TO USE, EASY TO SEE, EASY TO MOVE, AND EASY TO STORE

Ideal for any facility looking to ensure employees remain at safe distances, and our highly durable Waste Solutions are ideal for capturing any type of waste, including PPE.

MOBILE BARRIER / 7948069
SLIM JIM STEP ON 68L YELLOW / 7948075
SLIM JIM STEP ON 90L YELLOW / 7948085

WASTE SOLUTIONS AVAILABLE IN ***MULTIPLE SIZES AND COLOURS***

Rocol SAFE STEP® System

- A range of anti-slip solutions suitable for commercial and industrial environments - steps, stairs and floors
- Anti-slip tape is adhesive backed with a high grip, durable surface - suitable for use on most surfaces
- Anti-slip floor coatings are easy to apply and offer optimum adhesion to metal, concrete and timber surfaces

ROCOL

212-2461 Tape yellow 50mm x 18.25mm
290-1955 Tape grey 50mm x 18.25mm
290-1983 Tape grey 100mm x 18.25mm
425-1319 Rubber/alkyd resin grey
774-1036 Epoxy ester resin grey
774-1048 Epoxy ester resin yellow

Anti-slip PVC Mat

- COBAdot PVC floor mat with a smart studded surface, provides comfort underfoot and slip resistance
- Beneficial in reducing noise levels and adding an insulating surface on cold concrete floors
- Can be loose laid or bonded to the floor



COBA europe

325-564 10m x 1.2m (2.5mm thick)

Industrial Floor Tile

- Tough-Eco flooring is an easy and durable way to provide a comfortable working floor
- An ideal solution for warehouses, factories or workshops, able to withstand the weight of a forklift truck
- Tiles simply interlock for swift installation and can be cut to the desired layout



COBA europe

872-5678 500 × 500mm tile
872-5671 500mm tile edging

za.rs-online.com / www.rsonline.africa

First Aid Kits

- Fully stocked kits compliant with Health & Safety regulations
- Durable and robust case which can be easily carried to the casualty location

RS PRO

787-3426	1-10 people
787-3420	1-20 people
787-3439	1-50 people
787-3432	Wall bracket

Safety & Surveillance Mirrors

- Unbreakable polycarbonate multi-purpose mirror with 50mm visor for internal or external use
- 90° vision

RS PRO

663-4618	600mm
663-4612	800mm

Fire Alarm Call Points

- Fulleon break glass operation call points with monitoring resistor
- Superior LED alarm indication and certified to EN54-11

EATON Powering Business Worldwide

681-2815	Red
377-1783	Green

Security Cable & Locks

- Clear vinyl covered steel security cable ideal for securing equipment, gates, or other items
- Choice of matching keyed or combination all-weather padlocks for maximum security and peace of mind

ABUS Security Tech Germany

364-6069	1.85m cable
242-1847	2.0m cable
704-0086	83WP/53 keyed padlock
801-0702	158/65 combination padlock

Fire Safety Signs

- Environmentally friendly and durable
- 1.2mm Polypropolene
- SAV = Self Adhesive Vinyl - easy to peel and apply

RS PRO

763-1982	Vinyl
763-1973	Plastic
763-1856	PP
763-1929	PET
370-1116	PET

WHATEVER YOUR SIGNAGE NEEDS, WE CAN HELP

Exit Signage

- Designed to show the way out quickly and easily in an evacuation scenario
- Can be shown in words or images with or without arrows
- Available in a variety of sizes and mounting options

Mandatory Signage

- Mandatory signs used to inform people of the statutory requirements for the area they have entered
- These include safety, prohibition, warning or PPE signs

Fire Signage

- It is a legal requirement that all occupants of a building are aware of fire safety instructions
- These indicate fire doors and exits, fire alarms, fire assembly points and fire extinguishers

Prohibition Signage

- Essential for workplaces and public areas that require health and safety orders
- Signs include a red circle with the banned activity
- Available with a variety of messages

First Aid Signage

- Displayed to promote a safer environment by highlighting emergency first aid information
- Used to highlight location of first aid stations or equipment such as defibrillators

Safety Posters

- Selection of posters and wall charts to assist in identifying hazard areas and associated dangers
- Available in different languages and materials to suit different requirements



Security Signage

- Used across a multitude of public and private spaces to communicate the presence of security or surveillance systems
- Can be used as a deterrent to help prevent crime or for making visitors aware that their movements will be monitored

Warning Signage

- This is a legal requirement for all businesses where there is a potential risk
- Available in two colour combinations of yellow/amber with black text and images or red with white text and images